



MOUNTING INTERFACE



PERFORMANCES

(measured with mineral oil of viscosity 36cSt at 50°C)

Maximum operating pressure	bar	350
Minimum controlled pressure	see Δp diagram.	
Maximum flow rate in controlled lines and in the free lines	l/min	75
Ambient temperature range	°C	-20 / +60
Fluid temperature range	°C	-20 / +80
Fluid viscosity range	cSt	10 ÷ 400
Fluid contamination degree	According to ISO 4406:1999 class 20/18/15	
Recommended viscosity	cSt	25
Mass: MRQ-SP / MRQ-SAT / MRQ-SBT / MRQ-SB MRQ-DT / MRQ-D	kg	1,4 2,1

PILOT OPERATED PRESSURE RELIEF VALVE SERIES 51

MODULAR VERSION ISO 4401-03

p max 350 bar Q max 75 l/min

OPERATING PRINCIPLE



- The MRQ valve is a pilot operated pressure relief valve made as a modular version with mounting surface according to ISO 4401 standards.
- It can be assembled with all ISO 4401-03 modular valves without the use of pipes, using suitable tie-rods or bolts.
- It is available in versions for single adjustment on one control line or dual on two control lines and with four different pressure adjustment ranges.
- This valve is used as a hydraulic circuit pressure limiting device.
- It is supplied with a hexagonal socket screw, locking nut and limitation of the maximum adjustment travel or with adjustment knob.

HYDRAULIC SYMBOLS



1 - IDENTIFICATION CODE





3 - HYDRAULIC FLUIDS

Use mineral oil-based hydraulic fluids HL or HM type, according to ISO 6743-4. For these fluids, use NBR seals. For fluids HFDR type (phosphate esters) use FPM seals (code V). For the use of other kinds of fluid such as HFA, HFB, HFC, please consult our technical department. Using fluids at temperatures higher than 80 °C causes a faster degradation of the fluid and of the seals characteristics.

The fluid must be preserved in its physical and chemical characteristics.

4 - OVERALL AND MOUNTING DIMENSIONS

MOTION SOLUTIONS

a member of **DAIKIN** group



via Mario Re Depaolini, 24 | 20015 Parabiago (MI) | Italy T +39 0331 895111 | E vendite.ita@duplomatic.com | sales.exp@duplomatic.com duplomaticmotionsolutions.com

DUPLOMATIC MS Spa